




CDK12.5 - OPTICAL TRAIN: for FINGERLAKES PROLINE CAMERA AND FILTERWHEEL



Distance to Focuser Mounting Surface 10.45



FLI Proline, CFW5, and MonsterMOAG	10.45 remaining BF
2.75" Focuser (racked in)	3.25
SecureFit CCD Spacer - 125357-3	2.5
Adapter SecureFit to Monster MOAG - 200394	0.55
Monster MOAG - MMOAG	1.25
AstroDon Adapter	1.14
FLI CFW5 Filter Wheel	0.85
FLI Proline Camera Body	0.88




FLI Proline, CFW5, Monster MOAG, Pyxis	10.45 remaining BF
2.75" Focuser (racked in)	3.25
Optec Pyxis 3" Camera Field Rotator	2.4
Adapter SecureFit to Monster MOAG - 200394	0.55
Monster MOAG - MMOAG	1.25
AstroDon Adapter to 3"-24 thread, 5" long	0.5
Apogee FW50	0.85
Apogee Alta U16M CCD back focus	0.88



FLI Proline with CFWS/7	10.45 remaining BF
2.75" Focuser (racked in)	3.25
SecureFit CCD Spacer - 125357-3	4.8
SecureFit FLI 3" CCD Adapter - 200395	0.25
FLI CFWS/7 Filter Wheel	0.85
FLI Proline Camera Body	0.88

CDK17 and 20 - OPTICAL TRAIN: FINGERLAKES CAMERA'S AND FILTER WHEELS



FLI Proline Camera Body	8.81 remaining BF	
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.57	5.24
3.5" to SecureFit, 3.8" - 200361-1	3.8	1.44
SecureFit to FLI 3" Threads - 200395	0.25	1.19
FLI Proline Camera	1.19	0

FLI Proline Camera Body and CFW5 filter wheel	8.81 remaining BF	
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.84	4.98
3.5" to Securefit, 2.1" - 200361-2	2.5	2.48
SecureFit CCD Extender - 200377	0.5	1.98
SecureFit to FLI 3" Threads - 200395	0.25	1.73
FLI CFW5 Filter Wheel	0.85	0.88
FLI Proline Camera	0.88	

FLI Proline Camera, CFW5 filter wheel & MonsterMOAG	8.81 remaining BF	
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.65	5.16
Low Profile SecureFit Spacer - 600327 and 600328	0.5	4.66
Adapter SecureFit to Monster MOAG - 200394	0.55	4.11
Monster MOAG - MMOAG	1.25	2.86
AstroDon Adapter to FLI thread	1.14	1.73
FLI CFW5 Filter Wheel	0.85	0.88
FLI Proline Camera	0.88	

FLI Proline Camera, CFW4 filter wheel & MonsterMOAG	8.81 remaining BF	
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.71	5.1
Low Profile SecureFit Spacer - 600327 and 600328	0.5	4.6
Adapter SecureFit to Monster MOAG - 200394	0.55	4.05
Monster MOAG - MMOAG	1.25	2.8
AstroDon Adapter to FLI thread	1.14	1.66
FLI CFW4 Filter Wheel	0.79	0.88
Apogee Alta U16M CCD back focus	0.88	

